

MOTIP Effect Metallic

Technical Information



Fast-drying lacquer to treat surfaces of wood, metal, aluminium, glass, stone and various types of plastic. Metallic Lacquer is rub resistant, scratch free and wear-resistant and resistant to weather influences. MoTip Deco Effect Metallic Lacquer is available in 13 colours.

Ord.-no: 302501, 302502, 302503, 302504, 302505, 302506, 302507, 302508, 302509, 302510, 302511, 302512, 302513

Quality & properties

- Fast drying
- Rub resistant
- Non-fading and UV resistant
- Scratch free and shock proof
- Resistant to weather influences
- Wear-resistant
- Excellent adhesion

Physical & chemical data

Base: Nitrocombi resin

Colourname:

- brilliant silver
- aluminium
- sparkling silver
- silver
- gold
- brilliant gold
- real gold
- antique gold
- blue
- black
- red
- violet
- green

Degree of gloss: gloss GU

Efficiency: 400 ML – 1,25 - 1,75 m²

Dry to touch: 10 - 20 min

Dust dry:

- 5 - 10 min
- 5 min

Completely dry: 120 min

Overcoatable: 120 min

Surfaces: wood, metal, aluminium, glass, stone and various types of plastic

Minimum Working Temperature: 15 °C

Maximum Working Temperature: 25 °C

Flash point:

- n.a.
- 27 °C

Temperature Resistance: 110 °C

Content:

- 400 ML
- 400 ml
- 12 ML

How to use

The surface should be clean, dry and free of grease. Slightly sand the surface (grain 600).

The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 10 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimetre.

Apply the lacquer in several thin layers. Before applying the next layer, again shake the aerosol.

After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

The drying time depends on the ambient temperature, the humidity of the air and the thickness of the lacquer applied.

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

As of May 7, 2025 – This release replaces all eventually earlier issued versions.